

- Quick Links
- Cross reference
- RoHS/LF P/N Search
- Industry Standards
- Alphabetical List
- Documentation
- 3D model search
- Customer drawing search
- Multi Selection Search
- Search by category

Start > Search=10127817-122LF* > 10127817-122LF

10127817-122LF
10127817-122LF - Minitek® Pwr4.2 : Minitek® Pwr4.2 Female Terminal, Phosphorus Bronze, Tin plating, AWG #24-#28, Post-Plated



- Customer drawing
- Product Environmental Compliance Report

ACTIVE 48

RoHS Compliant

Distributor Stock

CORE RANGE

Print Datasheet

FCI Brings You More

- Contact our sales/technical support
- Sample request

- Specifications
- Download document

Dimensional General Electrical Mechanical Physical Other Features	
Dimensional	
Pitch	4.2
General	
Number of contacts	1
Series	10127817
Electrical	
Withstanding Voltage	1500 Vac, No breakdown. Current leakage < 5mA
Current rating	UP to 9 Amps
Resistance (Contact)	10 milliohm max.
Resistance (Insulation)	1000M ΩMin
Voltage rating	600V
Mechanical	
Durability (Mating cycles)	30 Cycles
Insertion force	14.7N max.
Withdrawal Force	1 N min.
Physical	
Material (Contact)	PhBr
Plating (Contact area)	Tin
Temperature (Range)	-40°C to +105°C
Other Features	
Packaging (Type)	Paper Reel

Disclaimer : The information above is for reference only. For more technical details, refer to product specification and application specification.