




TOP VIEW





SIDE VIEW



BOTTOM VIEW



Specifications			Notes	Revision History							
Description	Value	Unit		Version	Description		Date	Approved			
Shape	Rectangle		1) All dimensions are in mm unless otherwise noted 2) All parts meet RoHS	1	Released from Engineering		3/24/2015	J.S.			
Resonant Frequency	800	(Hz)									
Frequency Range	800 ~ 20,000	(Hz)									
SPL @ 10cm	89	(dBA)									
Capacitance	750	(nF)									
Diaphragm Material	Piezo										
Rated Voltage	7	(Vrms)									
Max Input Voltage	9	(Vrms)									
Mount Type	Flush Mount										
Operating Temperature	-20 ~ +70	°C									
Storage Temperature	-30 ~ +85	°C									
Weight	2	(g)									
							SZ300807-1				

Additional considerations can be found at www.dbunlimitedco.com/technical-articles.