



Part Number:	TE102803-1	
DRAWN	CJ	1/20/2017
CHECKED	P.D	1/20/2017
Description:	APPROVED	1/20/2017
	J.S	
This document contains data proprietary to DB Unlimited. Any use or reproduction, in any form, without prior written permission of DB Unlimited is prohibited. All terms and conditions can be found at www.dbunlimitedco.com		


Top View



Side View



Bottom View



Items	Specifications	Conditions
Sound Pressure Level	93	dB (@ 10cm)
Resonant Frequency	2,830	Hz
Rated Voltage	3.6	V
Voltage Range	3 ~ 4.5	V
Coil Resistance	18 ± 5	Ω
Max. Rated Current	100	mA
Storage Temperature	-40 ~ +85	°C
Operating Temperature	-40 ~ +85	°C
Connection Method	Surface Pads	
Mount Type	Surface Mount	
Housing Material	LCP	
Weight	0.8	g

REVISION HISTORY

REV	DESCRIPTION	DATE	APPROVED
	Released from Engineering	8/27/2014	J.S.
1	Updated to new template	1/20/2017	J.S.
2	Corrected voltage range and weight	5/18/2017	C.E.
3	Updated operating temperature	3/29/2021	J.S.

NOTES

- 1) All dimensions are in mm unless otherwise noted
- 2) All tolerances are ± 0.2 mm unless otherwise noted
- 3) All parts meet RoHS
- 4) Subject to change or redrawn without notice