




TOP VIEW





SIDE VIEW



BOTTOM VIEW



| Specifications | | | Notes | Revision History | | | | | | | |
|---|--------------------|-------|---|------------------|---------------------------|-------------------------------------|--------------------|--------------------|--------------------|--------------------|--------------------|
| Description | Value | Unit | | Version | Description | | Date | Approved | | | |
| Technology | Electro-Mechanical | | 1) All dimensions are in mm unless otherwise noted 2) All parts meet RoHS | 1 | Released from Engineering | | 10/21/2013 | J.S | | | |
| Resonant Frequency | 400 | (Hz) | | | | | | | | | |
| Rated Voltage | 9 | (V) | | | | | | | | | |
| SPL @ 10cm | 75 | (dBA) | | | | | | | | | |
| Tone | Single Tone | | | | | | | | | | |
| Mount Type | Thru Hole | | | | | | | | | | |
| Voltage Range | 6 ~ 12 | (V) | | | | | | | | | |
| Max Rated Current | 25 | (mA) | | | | | | | | | |
| Housing Material | ABS | | | | | | | | | | |
| Operating Temperature | -10 ~ +60 | °C | | | | | | | | | |
| Storage Temperature | -20 ~ +70 | °C | | | | | | | | | |
| Weight | 10 | (g) | | | | | | | | | |
|  DB UNLIMITED | | |  DB UNLIMITED | | | Electro-Mechanical Indicator | | | IE220409-1 | | |
| | | | | | | Drawn by A.B. | Date 10/21/2013 | Checked by C.E. | Date 10/21/2013 | Approved by J.S | Date 10/21/2013 |

Additional considerations can be found at www.dbunlimitedco.com/technical-articles.