





## M Seires Wiring Connectors Quick Splice Wire Connector Series





Electrical Performance & Material	
Model	PCT-2-1M / ML / MR
Number of holes	1(Can Be Spliced With Any Number Of Digits)
Rated Voltage	250V
Rated Current	32A
Strip Length	9-10mm/0.39in
Wiring size	Solid wire: 0.5-4mm <sup>2</sup>
	Strand wire: 0.4-2.5mm <sup>2</sup>
Wiring Method	Lever Crimp
Shell	Nylon / PC
Contact	Copper
Spring	High-Performance spring steel
Temperature	-25°C-85°C
Applications	Electrical Equipment Electrical Cabinet Wiring Connections



### Model Identification And Size




**PCT-2-1ML**  
Splice Buckle And Screw Holes Are **Not** On The Same Side




**PCT-2-1MR**  
Splice Buckle And Screw Holes Are On The Same Side



**PCT-2-1M**  
**Only** The Splice Buckle Has No Screw Fixing Holes



### How To Use



Splicing With Snaps And Card Slots



Nylon Regular



Color Lever



PC transparent