





**B06 Quick Wiring Connectors  
TERMINAL BLOCK SERIES**



**Product Appearance Size**



**B06-2P**



**B06-3P**



**B06-4P**




**B06-5P**

**Electrical Performance & Material**

Model	B06-2P/3P/4P/5P
Number of holes	2,3,4,5
Rated Voltage	450V
Rated Current	16A
Wiring size	0.5-2.5mm <sup>2</sup> (Flexible Stranded Conductors Require Terminal Wraps)
Wiring method	Crimp
shell	Nylon
Contact	Copper
Spring	High-Performance spring steel
Temperature	-25°C-85°C
Applications	Wire Branch and connection

Please Pay Attention To The Difference Between These Two Products:

- 1.The Height Of The Product With "J" Pin Is 22.5mm
- 2.The One With "J" Pin Can Be Directly Fixed On The Panel



More Than 3 Holes Can Be Optionally Equipped With Grounding Lugs (Optional)