




TOP VIEW




SIDE VIEW



BOTTOM VIEW



Specifications			Notes	Revision History					
Description	Value	Unit		Version	Description		Date	Approved	
Technology	Electro-Mechanical		1) All dimensions are in mm unless otherwise noted 2) All parts meet RoHS  DB UNLIMITED	1	Released from Engineering		10/21/2013	J.S	
Resonant Frequency	2,500	(Hz)							
Rated Voltage	3	(V)							
SPL @ 10cm	73	(dBA)							
Tone	Single								
Mount Type	Thru Hole								
Voltage Range	2 ~ 5	(V)							
Max Rated Current	20	(mA)							
Housing Material	NORYL								
Operating Temperature	-25 ~ +70	°C							
Storage Temperature	-25 ~ +70	°C							
Weight	1	(g)							
				Electro-Mechanical Indicator		IE092503-1			
				Drawn by	Date	Checked by	Date	Approved by	Date
				A.B.	10/21/2013	C.E.	10/21/2013	J.S	10/21/2013

Additional considerations can be found at www.dbunlimitedco.com/technical-articles.