




TOP VIEW




SIDE VIEW



BOTTOM VIEW



| Specifications | | | Notes | Revision History | | | | | | |
|--|--------------------|-------|--|------------------|---------------------------|-------------------|------------|----------|--|--|
| Description | Value | Unit | | Version | Description | | Date | Approved | | |
| Technology | Electro-Mechanical | | 1) All dimensions are in mm unless otherwise noted 2) All parts meet RoHS | 1 | Released from Engineering | | 10/21/2013 | J.S | | |
| Resonant Frequency | 2,731 | (Hz) | | | | | | | | |
| Rated Voltage | 1.5 | (V) | | | | | | | | |
| SPL @ 10cm | 80 | (dBA) | | | | | | | | |
| Coil Resistance | 5.5 | (ohm) | | | | | | | | |
| Mount Type | Thru-hole | | | | | | | | | |
| Voltage Range | 1 ~ 3 | (V) | | | | | | | | |
| Max Rated Current | 80 | (mA) | | | | | | | | |
| Housing Material | PBT | | | | | | | | | |
| Operating Temperature | -30 ~ +70 | °C | | | | | | | | |
| Storage Temperature | -40 ~ +85 | °C | | | | | | | | |
| Weight | 1 | (g) | | | | | | | | |
|  DB UNLIMITED | | | Electro-Mechanical Transducer | | | TE092701-3 | | | | |
| | | | | | | | | | | |

Additional considerations can be found at www.dbunlimitedco.com/technical-articles.