



TOP VIEW



SIDE VIEW



Specifications			Notes	Revision History					
Description	Value	Unit		Version	Description		Date	Approved	
Resonant Frequency	2,900	(Hz)		1	Released from Engineering		10/21/2013	J.S	
Resonant Impedance (Max)	500	(Ohm)							
Max Input Voltage	30	(V)							
Capacitance	23,000	(pF)							
Plate Material	Brass								
Operating Temperature	-20 ~ +70	°C							
Storage Temperature	-30 ~ +80	°C							
</									

Additional considerations can be found at www.dbunlimitedco.com/technical-articles.