




TOP VIEW




SIDE VIEW



BOTTOM VIEW



Specifications			Notes	Revision History							
Description	Value	Unit		Version	Description		Date	Approved			
Technology	Piezo		1) All dimensions are in mm unless otherwise noted 2) All parts meet RoHS	1	Released from Engineering		10/21/2013	J.S			
Resonant Frequency	3,500	(Hz)									
Rated Voltage	12	(V)									
SPL @ 10cm	89	(dBA)									
Mount Type	Thru Hole										
Voltage Range	3 ~ 18	(V)									
Max Rated Current	15	(mA)									
Housing Material	PBT										
Operating Temperature	-20 ~ +60	°C									
Storage Temperature	-30 ~ +70	°C									
Weight	1.7	(g)									
			 DB UNLIMITED	Piezo Transducer			TP223512-1				
				Drawn by A.B.		Date 10/21/2013	Checked by C.E.		Date 10/21/2013	Approved by J.S	

Additional considerations can be found at www.dbunlimitedco.com/technical-articles.