


Model 3750, 3760 & 3770 **Standard Binding Post**

CE





FEATURES:

- Accepts standard banana plug, wire or spade lug.
- Mounts in panels from .070" to .250" (1.77mm to 6.35mm) thick.

MATERIALS:

Insulated Captive Thumb Nut: Brass

Insulation: Polycarbonate Mounting Base: Polycarbonate Insulator: Polycarbonate

Lockwasher: Nickel Plated Steel Hex Nut: 1/4" #8-32 Nickel Plated Brass

Binding Post:

Finish: 3750 – Gold plated brass, 3760 – Bright tin plated brass, 3770 – Gold plated Tellurium Copper

RATINGS:

Operating Voltage: Hands free usage in controlled voltage environments: 2500 Vrms maximum. For CE compliance: not

intended for hand-held use at voltage above 33 Vrms/70 Vdc.

Operating Temperature: +239°F (+115°C) Max.

Current: 15 Amperes

ORDERING INFORMATION:

Model: 3750-Color (Gold plated brass) Available in Colors* =: 0 (Black, 2 (Red), 3 (Orange), 4 (Yellow), 5 (Green), 6 (Blue), 9 (White)

Model: 3760-Color (Bright tin plated brass) Available in Colors =: 0 (Black), -2 (Red) 3 (Orange), 4 (Yellow),

5 (Green), 6 (Blue), 7 (Violet), 8 (Gray), 9 (White)

Model: 3770-Color (Gold Plated Tellurium Copper) Colors* =: 0 (Black), -2 (Red) 8 (Gray), 9 (White)

*Upon request other colors can be quoted.

All dimensions are in inches. Tolerances (except noted): $.xx = \pm .02$ " (,51 mm), $.xxx = \pm .005$ " (,127 mm). All specifications are to the latest revisions. Specifications are subject to change without notice. Registered trademarks are the property of their respective companies

Sales: 800-490-2361 Fax: 888-403-3360 Technical Support: 800-241-2060 (technical support@pomonatest.com) For "Where to Buy" information, visit the Pomona web site at www.pomonaelectronics.com

D1093975, D1093981, D1093927