

## RJ45 overmolded patch cable Cat 6 20,0m



Image is for illustration purposes only.  
Please refer to product description.

|  |                                     |
|--|-------------------------------------|
| <b>Part number:</b>                                    | 09 47 474 7123                      |
| <b>Description:</b>                                    | RJ45 overmolded patc<br>Cat 6 20,0m |
| <b>RoHS conformity:</b>                                | Yes                                 |
| <b>Limiting temperature (flexible),<br/>min.:</b>      | 0 °C                                |
| <b>Limiting temperature (flexible),<br/>max.:</b>      | 60 °C                               |
| <b>Limiting temperature, min.:</b>                     | -20 °C                              |
| <b>Limiting temperature, max.:</b>                     | 80 °C                               |
| <b>Degree of protection acc. to DIN<br/>EN 60 529:</b> | IP 20                               |
| <b>Cable length:</b>                                   | 20 m                                |
| <b>Material, cable:</b>                                | SF/UTP, PUR                         |