



WIRING TABLE

C1	WIRE	C2
1	AWG 30	1
2	AWG 30	2
3	AWG 30	3
-	AWG 30	-
19	AWG 30	19
20	AWG 30	20

C1 HAR-FLEX 20 POLE FEMALE CONNECTOR WITH STRAIN RELIEF

C2 HAR-FLEX 20 POLE FEMALE CONNECTOR WITH STRAIN RELIEF

FLAT CABLE,UL2678,AWG30,20CORE

NOTES:

- 1.)CABLE MUST BE PERFORMED 100% CONTINUITE TEST AND HI-POT(500VDC)TEST.
- 2.)CABLE OPERATION TEMPERATURE: -20°C TO +105°C
- 3.)CABLE SHOULD BE PACKED BY THE PLASTIC BAG,THEN PUT IT INTO THE CARTON (QTY ACCORDING TO ACTUAL CONDITION) EXPORT CARTON SHOULD BE STICKED THE LABEL WITH P/N AND QTY.
- 4.)WHITE LABEL CONTENT:

DATA CODE  
HARTING P/N

HARTING P/N	REVISION	Cable length ( L )
3315 243 010 0177	00	100 ± 3
3315 243 020 0177	00	200 ± 3
3315 243 050 0177	00	500 ± 5

	All Dimensions in mm Original Size DIN A3		Scale 2:1	Free size tol. \		Ref. \
	All rights reserved Department HCS - CN		Created by LIT	Inspected by	Standardisation	Sub. \
HARTING Customised Solutions D-32339 Espelkamp		Title Har-Flex 20Pole,Dul-end,With SR,L=XXMM			Date 2015-06-09	State In Work
		Type TB	Number 33 15 243 XXX0177		Doc-Key / ECM-Nr. 100625348/UGD/000/A	Rev. A Page 1/1

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HARTING:](#)

[33152430200177](#) [33152430500177](#) [33152430100177](#)