



M12 A-coded 3-poles, male straight connector

M12 A-coded 3-poles, female straight connector



length in "1m" step	40	XXX=400
	39	XXX=390
	.	.
	12	XXX=120
length in "0,1m" step	11	XXX=110
	10	XXX=100
	9,9	XXX=099
	9,8	XXX=098
	.	.
	0,4	XXX=004
	0,3	XXX=003
	0,2	XXX=002
	0,1	XXX=001
Step	a [m]	XXX

4,0 to 40	+1%
0,1 to 3,9	+0,04
a [m]	Tolerance

Part no.	213484853XXXXX
-----------------	----------------

Type of cable	XX
PVC grey, 3x0,34mm ²	XX=83
PUR black, 3x0,34mm ²	XX=90

- Protection level: IP67
 - Temperature range: -25°C ... +80°C

All rights reserved Department EC PD - RO		All Dimensions in mm Original Size DIN A3	Scale 2:1	Free size tol.	Ref. Sub.
HARTING Electronics GmbH D-32339 Espelkamp	Created by TOMUTA	Inspected by AVRAM	Standardisation HOFFMANN	Date 2014-07-29	State Final Release
Title M12 A-coded Cable Assembly				Doc-Key / ECM-Nr. 100578704/UGD/009/B 50000078282	
Type TB		Number 213484853XXXXX		Rev. B	Page 1/1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

HARTING:

[21348485390050](#) [21348485390010](#) [21348485383050](#) [21348485383010](#) [21348485383005](#) [21348485383075](#)
[21348485383100](#) [21348485390075](#) [21348485383015](#) [21348485390015](#) [21348485390100](#) [21348485390005](#)
[21348485383020](#) [21348485390020](#)