

PIN RECEPTACLES

FOR .048" - .064" DIAMETER PINS (#13 CONTACT)
FOR .045" - .065" DIAMETER PINS (#23 CONTACT)

<p>0364 0364-0-15-XX-13-XX-10-0 Solder mount in .100 min. mounting hole Also available on 16mm wide carrier tape: 1,300 parts per 13" reel See page 194.13 for Tape & Reel details</p>	<p>0363 0363-0-15-XX-23-XX-10-0 Solder mount in .102 min. mounting hole</p>	<p>0365 0365-0-15-XX-23-XX-10-0 Hex press-fit in .105 plated through-hole Also available on 16mm wide carrier tape: 1,200 parts per 13" reel See page 194.14 for Tape & Reel details</p>	<p>0366 0366-0-15-XX-13-XX-10-0 Press-fit in .109 mounting hole</p>
<p>0372 0372-0-15-XX-13-XX-10-0 Solder mount in .102 min. mounting hole Also available on 24mm wide carrier tape: 950 parts per 13" reel See page 194.14 for Tape & Reel details</p>	<p>0362 0362-0-15-XX-X3-XX-10-0 Solder mount in .102 min. mounting hole</p>	<p>0367 0367-0-15-XX-23-XX-10-0 Square press-fit in .040 plated through-hole</p>	<p>9324 9324-0-15-XX-23-XX-04-0 Press-fit in .106 mounting hole</p>
<p>0492 0492-0-15-XX-13-XX-04-0 Press-fit in .106 mounting hole</p>	<p>0381 0381-0-15-XX-23-XX-10-0 Press-fit in .104 mounting hole</p>	<p>4034 4034-0-15-XX-23-XX-04-0 Press-fit in .109 mounting hole</p>	<p>3044 3044-0-15-XX-23-XX-04-0 Solder mount in .104 min. mounting hole</p>

SPECIFICATIONS:

Shell Material: Brass Alloy 360, 1/2 Hard

Contact Material: Beryllium Copper Alloy 172, HT

Dimensions: Inches

Tolerances On: Lengths: ±.005

Diameters: ±.002

Angles: ± 2°



ORDER CODE: XXXX - X - XX - XX - XX - XX - XX - 0

BASIC PART #

SPECIFY SHELL FINISH:

- 01 200 μ" TIN/LEAD OVER NICKEL
- ◆ 80 200 μ" TIN OVER NICKEL (RoHS)
- ◆ 15 10 μ" GOLD OVER NICKEL (RoHS)

SPECIFY CONTACT FINISH:

- 01 200 μ" TIN/LEAD OVER NICKEL
- ◆ 80 200 μ" TIN OVER NICKEL (RoHS)
- ◆ 27 30 μ" GOLD OVER NICKEL (RoHS)

SELECT CONTACT:

#13 or #23 CONTACT (DATA ON PAGE 260)

(For alternate contact choices, see group G on page 248)



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Mill-Max:](#)

[0492-0-15-80-13-27-04-0](#) [0372-0-15-80-13-80-10-0](#) [0365-0-15-80-23-27-10-0](#) [0364-0-15-80-13-80-10-0](#) [0366-0-15-13-27-10-0](#) [9324-0-15-80-23-80-04-0](#) [9324-0-15-80-23-27-04-0](#)