


RECOMMENDED PCB LAYOUT
THICKNESS : 1.0 mm



Material
Housing: LCP, UL 94 V-0, Black.
Contact: Copper Alloy, Gold
Contact Type: Stamped
Shielding: Stainless Steel Matt Tin Plated.

Electrical:
Current Rating: 1.8 A Pin1 & Pin 5
1.0 A Other Pins
Voltage Rating: 30V DC
Contact Resistance: 30mΩ Max.
Withstanding Voltage: 100 Vac/Min.
Insulation Resistance: 1000MΩ Min.
Operating Temperature: -40°C Up To +85°C
Compliance: Lead Free And Rohs

Order Information

L-KLS1- 2233B - B
Color: B=Black
Micro USB
RoHS

GENERAL TOLERANCE	PROJECTION		Description:
X. ±0.50	UNITS	mm	CONN RCPT 5POS MICRO USB Straight
.X ±0.25	SCALE	1:1	
.XX ±0.10	Draw by:	Jenny	KLS P/N: L-KLS1-2233B-B
ANGLE TOLERANCE	Check by:		NingBo KLS ELECTRONIC CO.,L TD.
X. ±5°	Date	2018-03-01	
.X ±3°	SHEET	1 OF 1	
.XX ±2°			