



THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION
 © COPYRIGHT - By - ALL RIGHTS RESERVED.

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
L3		REVISED PER ECR-15-018167	14JAN16	I.T	W.H



	D	C	B	A	NO OF POSN	PART NUMBER
	92.46 [3.640]	90.17 [3.550]	88.04 [3.466]	81.79 [3.220]	64	1-111547-3
NON AVAILABLE	87.38 [3.440]	85.09 [3.350]	82.96 [3.266]	76.71 [3.020]	60	1-111547-2
	74.68 [2.940]	72.39 [2.850]	70.26 [2.766]	64.01 [2.520]	50	1-111547-1
	67.06 [2.640]	64.77 [2.550]	62.64 [2.466]	56.39 [2.220]	44	1-111547-0
	61.98 [2.440]	59.69 [2.350]	57.56 [2.266]	51.31 [2.020]	40	111547-9
	54.36 [2.140]	52.07 [2.050]	49.94 [1.966]	43.69 [1.720]	34	111547-8
	49.28 [1.940]	46.99 [1.850]	44.86 [1.766]	38.61 [1.520]	30	111547-7
	44.20 [1.740]	41.91 [1.650]	39.78 [1.566]	33.53 [1.320]	26	111547-6
	41.66 [1.640]	39.37 [1.550]	37.24 [1.466]	30.99 [1.220]	24	111547-5
	36.58 [1.440]	34.29 [1.350]	32.16 [1.266]	25.91 [1.020]	20	111547-4
	31.50 [1.240]	29.21 [1.150]	27.08 [1.066]	20.83 [.820]	16	111547-3
	28.96 [1.140]	26.67 [1.050]	24.54 [.966]	18.29 [.720]	14	111547-2
	23.88 [.940]	21.59 [.850]	19.46 [.766]	13.21 [.520]	10	111547-1

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN H MOLL 10-23-90	PART NO	
DIMENSIONS: INCHES		CHK R.STONE 11-7-90	TE Connectivity	
TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± - 1 PLC ± - 2 PLC ± 0.13[.005] 3 PLC ± - 4 PLC ± - ANGLES ± -		APVD F.M.HEINEY 11-7-90	NAME STRAIN RELIEF, UNIVERSAL PIN CONNECTOR, AMP-LATCH	
MATERIAL GLASS FILLED POLYESTER, BLACK		FINISH -	PRODUCT SPEC 108-1336	RESTRICTED TO -
		APPLICATION SPEC 114-7011	SIZE A2	CAGE CODE 00779
		WEIGHT 0	DRAWING NO C=111547	SCALE 8:1
		CUSTOMER DRAWING	SHEET 1 of 1	REV L3

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[111547-9](#)