


# push-in T-connector QSMT-6-4

Part number: 153369

★ Core product range

FESTO



## Data sheet

| Feature                                       | Value  |
|---|--|
| Size  | Mini   |
| Nominal size                                  | 2.6 mm   |
| Assembly position                             | Any  |
| Container size                                | 10   |
| Design structure                              | Push/pull principle  |
| Operating pressure complete temperature range | -0.95 ... 6 bar  |
| Temperature dependent operating pressure      | -0.95 ... 14 bar   |
| Operating medium                              | Compressed air in accordance with ISO8573-1:2010 [7:-:-]             |
| Note on operating and pilot medium            | Lubricated operation possible  |
| Corrosion resistance classification CRC       | 1 - Low corrosion stress   |
| Ambient temperature                           | -10 ... 80 °C  |
| Maritime classification                       | see certificate  |
| Product weight                                | 4 g  |
| Number of outputs                             | 2  |
| Number of supply lines                        | 1  |
| Pneumatic connection, port 1                  | for tubing, 6mm outside diameter                                     |
| Pneumatic connection, port 2                  | For tubing outside diameter 4 mm<br>For tubing outside diameter 6 mm |
| Colour of release ring                        | blue   |
| Materials note                                | Conforms to RoHS   |
| Material housing                              | PBT  |
| Material release ring                         | POM  |
| Material of tubing seal                       | NBR  |
| Material of tube retaining claw               | High alloy steel, non-corrosive                                      |