

Detailed Specifications

| | |
|------------------------------------|--------------------------------|
| Frame Width: | 60[mm] |
| Frame Height: | 60[mm] |
| Frame Depth: | 20[mm] |
| Max. Air Flow: | 24.6[CFM] |
| Max. Air Flow: | 0.7[m3 per min] |
| Max. Static Pressure: | 0.4[In H2O] |
| Max. Static Pressure: | 100[Pa] |
| Fan Speed: | 6900[RPM] |
| Noise: | 42[dB] |
| Life Expectancy: | 25 degree C 100,000 Hours[L10] |
| Bearing Type: | Ball Bearing |
| Nominal Voltage: | 24[V] |
| Operating Voltage - Lower: | 10[V] |
| Operating Voltage - Upper: | 26.4[V] |
| Current: | 0.15[A] |
| Input Power: | 3.6[W] |
| Mass: | 80[g] |
| IP Rating: | IP68/IP69K |
| Tach / Locked Rotor Output: | No |
| Status: | Active |

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[NMB Technologies:](#)

[06020VA-24Q-CAS-0](#)