


Data Sheet | Item Number: 264-734
4-conductor miniature through terminal block; 2.5 mm²; with test option; suitable for Ex i applications; center marking; for DIN-rail 35 x 15 and 35 x 7.5; CAGE CLAMP®; 2,50 mm²; blue
<https://www.wago.com/264-734>



Color:  blue

Similar to illustration



Similar to illustration

Electrical data

Ratings per IEC/EN		Power loss	
Nominal voltage (III/3)	800 V	Power loss, per pole (potential)	0.7661 W
Rated impulse voltage (III/3)	8 kV	Rated current I _N for specified power loss	24 A
Rated current	24 A	Resistance value for specified, current-dependent power loss	0.00133 Ω
Legend (ratings)	(III / 3) ≙ Overvoltage category III / Pollution degree 3		

Connection data

Connection 1	
Connection points	4
Total number of potentials	1
Number of levels	1
Connection technology	CAGE CLAMP®
Actuation type	Operating tool
Connectable conductor materials	Copper
Solid conductor	0.08 ... 2.5 mm² / 28 ... 12 AWG
Fine-stranded conductor	0.08 ... 2.5 mm² / 28 ... 12 AWG
Note (conductor cross-section)	12 AWG: THHN, THWN
Strip length	8 ... 9 mm / 0.31 ... 0.35 inches
Wiring direction	Front-entry wiring

Physical data

Width	10 mm / 0.394 inches
Height	38 mm / 1.496 inches
Depth from upper-edge of DIN-rail	24.5 mm / 0.965 inches



Mechanical Data		
Design	horizontal type	
Mounting type	DIN-35 rail	
Marking level	Center marking	

Material Data		
Note (material data)	Information on material specifications can be found here	
Color	blue	
Material group	I	
Insulation material	Polyamide (PA66)	
Flammability class per UL94	V0	
Fire load	0.108 MJ	
Weight	6.2 g	

Environmental requirements		
Processing temperature	-35 ... +85 °C	
Continuous operating temperature	-60 ... +105 °C	

Commercial data		
Product Group	9 (Std Chassis Mt Blocks)	
eCl@ss 10.0	27-14-11-20	
eCl@ss 9.0	27-14-11-20	
ETIM 8.0	EC000897	
ETIM 7.0	EC000897	
PU (SPU)	100 pcs	
Packaging type	Box	
Country of origin	CH	
GTIN	4044918414944	
Customs tariff number	85369010000	

1 Compatible Products		
1.1 Required Accessories		
1.1.1 End plate		
1.1.1.1 End plate		



[Item No.: 264-368](#)
End and intermediate plate; 4 mm thick;
gray

[Item No.: 264-369](#)
End and intermediate plate; 4 mm thick;
orange