

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0039000061](#)
Status: **Active**
Overview: [Mini-Fit Jr. Power Connectors](#)
Description: Mini-Fit Male Crimp Terminal, Tin (Sn) over Phosphor Bronze, 18-24 AWG, Reel

Documents:

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

General

Product Family	Crimp Terminals
Series	5558
Application	Power, Wire-to-Wire
Crimp Quality Equipment	Yes
Overview	Mini-Fit Jr. Power Connectors
Packaging Alternative	39000062 (Loose)
Product Name	Mini-Fit
UPC	800753584686

Physical

Durability (mating cycles max)	30
Gender	Male
Material - Metal	Phosphor Bronze
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Net Weight	0.120/g
Packaging Type	Reel
Plating min - Mating	0.889µm
Plating min - Termination	0.914µm
Termination Interface: Style	Crimp or Compression
Wire Insulation Diameter	1.30-3.10mm
Wire Size AWG	18, 20, 22, 24
Wire Size mm ²	N/A

Electrical

Current - Maximum per Contact	9.0A
Voltage - Maximum	600V

Material Info

Engineering Number	5558PBT
--------------------	---------



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
D(2020)4578-DC (25
June 2020)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Not Relevant

Not Contained

Search Parts in this Series

[5558](#) Series

Use With

Mini-Fit Jr. Plug Housing [5559](#)
Mini-Fit
BMI Plug Housing [42475](#)

Application Tooling | FAQ

Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global

Description	Product #
Extraction Tool	11030044
FineAdjust Applicator for Mini-Fit Double Crimp Applications Using Two 22 AWG Wires	2037026300
Hand Crimp Tool for Mini-Fit Jr. Male and Female Crimp	638190901

Terminals, 18-24
 AWG
 FineAdjust Applicator 639015600
 for Insulation OD
 1.90-2.30mm - 18-24
 AWG
 FineAdjust Applicator 639023900
 for Insulation OD
 1.40-1.70mm - 18-24
 AWG
 FineAdjust Applicator 639024800
 for Insulation OD
 2.50-2.95mm
 Optimized for 18
 AWG Only
 FineAdjust Applicator 639024900
 for Insulation OD
 2.30-2.60mm - 18-24
 AWG
 FineAdjust Applicator 639047800
 for Insulation OD
 2.50-2.95mm, 18-24
 AWG
 FineAdjust Applicator 639048000
 for Insulation OD
 1.65-2.05mm, 18-24
 AWG
 T2 Terminator 639115600
 for insulation OD
 1.90-2.30mm - 18-24
 AWG
 T2 Terminator 639123900
 for insulation OD
 1.40-1.70mm - 18-24
 AWG
 T2 Terminator 639124800
 for insulation OD
 2.50-2.95mm
 optimized for 18
 AWG only
 T2 Terminator 639124900
 for insulation OD
 2.30-2.60mm - 18-24
 AWG
 T2 Terminator 639147800
 for Mini-Fit Crimp
 Terminals, 18-24
 AWG with Large
 Insulation ODs
 T2 Terminator 639148000
 for Mini-Fit Crimp
 Terminals, 18-24
 AWG with Smaller
 Insulation ODs

Japan

Description	Product #
S-1 Applicator for Mini-Fit Plug and Receptacle Terminals, 18-24 AWG, UL1007 Wires	<u>570223700</u>
S-1 Applicator for Mini-Fit Plug and Receptacle	<u>570223710</u>

This document was generated on 10/30/2020

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION