



+ CABLE ASSEMBLIES

PLUGGABLE I/O CABLE ASSEMBLIES



✓ Active

↓ **PRODUCT DRAWING**
English

TE CONNECTIVITY (TE) CA MINI IO TYPE II PIGTAIL

2205130-3
TE Internal Number: 2205130-3

Always EU RoHS/ELV Compliant

Cable Assembly Type **Mini I/O**

Equalized **No**

Wire Size (AWG) **26**

Wire Size (mm²) **.129**

Overall Outside Cable Diameter **.244 in, 6.2 mm**



Product Drawings

CA MINI IO TYPE II PIGTAIL

PDF
English

Please review product documents or [contact us](#) for the latest agency approval information. Please Note: Use the Product Drawing for all design activity.

Product Type Features

Cable Assembly Type	Mini I/O
Shielded	Yes
Connector Type (End A)	RJ45 Plug
Product Type	Cable Assembly
Cable Assembly Category	Industry Standard
Product Designation	Patch Cord



	Performance Category	Category 5E Performance for 10/100/1000BASE-T
	Latching Style	Slide Latch
	Twisted Pairs	Yes
Configuration Features	Number of Positions	8
	Number of Signal Positions	8
	Configuration	Single-Ended
Electrical Characteristics	Impedance (Ω)	100
Signal Characteristics	Data Rate (Gb/s)	1
Body Features	Equalized	No
	Color	Black
	Shield Material	Copper Alloy
	Jacket Material	PVC
Contact Features	Contact Mating Area Plating Material	Gold
	Contact Mating Area Plating Thickness	.5 μm, 19.68 μin
Mechanical Attachment	Jackscrew	Without
Housing Features	Housing Material	Thermoplastic
Dimensions	Wire Size (AWG)	26
	Wire Size (mm ²)	.129
	Overall Outside Cable Diameter	.244 in, 6.2 mm
	Cable Assembly Length	2 m [6.56 ft]
Operation/Application	Halogen Free	Yes
Industry Standards	Flammability Rating	UL 444
	IEEE 1394	No
Other	CLOUDSPLITTER	No

Product Compliance

Statement of Compliance

PDF

[VIEW ALL PRODUCT COMPLIANCE](#)

