

## Parallel female thread twin coupler



### Technical characteristics

**Technology:** "One push" safety system (avoids hose whip)

**Operating pressure:** 2 to 12 bar


**Flow rate at 6 bar:** 833 l/min ( $\Delta P = 0,6$  bar)

**ID Passage:** 6 mm

**Temperature:** -15°C to +70°C

**Construction:** Composite body

**Highlight:** Anti-static, Non scratch

	A (mm)	B (mm)	C (mm)	BSPP female thread	Parts Numbers
	134	82	17	G 1/4	<b>ISI 068101</b>
	140	87	20	G 3/8	<b>ISI 068102</b>
	150	95	25	G 1/2	<b>ISI 068103</b>