



**120W**

VT-9-120 120W HIGHBAY(MEANWELL DRIVER)WITH SAMSUNG CHIP  
 COLORCODE:4000K 5 YRS WARRANTY

Lumens <b>21600</b>	Beam Angle <b>120</b>	Dimensions <b>Ø260x145mm</b>
------------------------	--------------------------	---------------------------------

Day White  
 SKU:568




### Technical Information

Instant Start: 1-10V	LED Chip Type: SMD
Watts: 120	IP Rating: IP65
Lumens: 21600	Dimmable: No
Beam Angle: 120	Warranty (Years): 5
Unit Color: Black	PF: >0.9
Body Type: Aluminum	CRI: >80
Long life: 30,000 Hours	Input Power: AC:100-277V,50/60Hz

### Features

- ✓ Powerful LED light source with a unique design
- ✓ High Power LED Samsung Chip
- ✓ Reflector options of beam angle 90°D / 120°D
- ✓ High Lumen highbay with Meanwell Driver - 1-10V Dimmable
- ✓ Longevity and efficient lumen Maintenance
- ✓ High Thermal Conductivity, Low Luminous Decay, Pure Colours & No Heavy Shade
- ✓ Complies with LM-80
- ✓ Applications - Industrial Usage, Warehouse & Super Markets, Workshop's, Factories, Warehouse's and many more

Note:  Suitable & Recommended for maximum daily use of 10-12 hours, usage beyond this would void the warranty

## Packaging

### Listing Details

EAN Code

3800157633321

READY STOCKS IN  
**UK & EU**



Dispatch within  
**24** Hours

[www.vtacexports.com](http://www.vtacexports.com)

OUR PRODUCTS ARE  
CURRENTLY SOLD IN OVER

**70**

COUNTRIES