

Stewart Connector Modular Plug

Quick Reference Guide

						Low Volume Terminations	High Volume Factory Terminations		
Part Number	Performance	Shield	Strain Relief Boot	Cable Diameter	Conductor Diameter	Installation Hand Tool Kit	Production Hand Tool	Production Die Set	Termination Instructions
SS-39100-028	CAT6a	No	Slimline Included	.300" [7.62] Max	.033"-.038" [0.84 - 0.97]	2990003-01	2940231-01	2905014-01	MN390014.PDF
SS-39100-029	CAT6a	No	Not Included	.235" [5.97] Max	.037"-.042" [0.94 - 1.07]	2990003-01	2940231-01	2905014-01	MN390014.PDF
SS-39100-030	CAT6a	No	Not Included	.235" [5.97] Max	.033"-.038" [0.84 - 0.97]	2990003-01	2940231-01	2905014-01	MN390014.PDF
SS-39100-031	CAT6a	No	Slimline Included	.300" [7.62] Max	.037"-.042" [0.94 - 1.07]	2990003-01	2940231-01	2905014-01	MN390014.PDF
SS-39200-020	CAT6a	Yes	Slimline Included	.220"-.240" [5.59 - 6.10]	.037"-.042" [0.94 - 1.07]	N/A	2980070-01*		MN390011.PDF
SS-39200-021	CAT6a	Yes	Not Included	.220"-.240" [5.59 - 6.10]	.037"-.042" [0.94 - 1.07]	N/A	2980070-01*		MN390011.PDF
SS-39200-022	CAT6a	Yes	Slimline Included	.230"-.250" [5.84 - 6.35]	.037"-.042" [0.94 - 1.07]	N/A	2980075-01*		MN390011.PDF
SS-39200-023	CAT6a	Yes	Not Included	.230"-.250" [5.84 - 6.35]	.037"-.042" [0.94 - 1.07]	N/A	2980075-01*		MN390011.PDF
SS-39200-024	CAT6a	Yes	Slimline Included	.230"-.250" [5.84 - 6.35]	.033"-.038" [0.84 - 0.97]	N/A	2980075-01*		MN390011.PDF
SS-39200-027	CAT6a	Yes	Slimline Included	.270"-.295" [6.86 - 7.49]	.042"-.048" [1.07 - 1.22]	N/A	2980078-01*		MN390015.PDF
SS-39100-008	CAT6	No	Slimline Included	.220"-.230" [5.59 - 5.84]	.037"-.042" [0.94 - 1.07]	2990009-01	2940231-01	2905029-01	MN390006.PDF
SS-39100-011	CAT6	No	Slimline Included	.240"-.250" [6.10 - 6.35]	.037"-.042" [0.94 - 1.07]	2990009-01	2940231-01	2905029-01	MN390006.PDF
SS-39100-021	CAT6	No	Not included - See boot PN: 450-034	.235" [5.97] Max	.037"-.042" [0.94 - 1.07]	2990003-01	2940231-01	2905014-01	MN390010.PDF
SS-39100-039	CAT6	No	Slimline Included	.160" [4.06] Max	.025"-.030" [0.64 - 0.76]	2990003-01	2940231-01	2905014-01	MN390017.PDF
SS-39200-010	CAT6	Yes	Not Included	.240"-.260" [6.10 - 6.60]	.037"-.042" [0.94 - 1.07]	N/A	2980075-01*		MN390009.PDF
SS-39200-011	CAT6	Yes	Included	.232"-.248" [5.90 - 6.30]	.037"-.042" [0.94 - 1.07]	N/A	2980075-01*		MN390009.PDF
SS-39200-012	CAT6	Yes	Not Included	.220"-.240" [5.59 - 6.10]	.037"-.042" [0.94 - 1.07]	N/A	2980070-01*		MN390009.PDF
SS-39200-015	CAT6	Yes	Included	.220"-.240" [5.59 - 6.10]	.037"-.042" [0.94 - 1.07]	N/A	2980070-01*		MN390009.PDF
SS-39200-019	CAT6	Yes	Not included - See boot PN: 39200-883	.270"-.295" [6.86 - 7.49]	.037"-.042" [0.94 - 1.07]	N/A	2980078-01*		MN390009.PDF
SS-37000-007	CAT5E	No	Not included - See boot PN: 450-034	.235" [5.97] Max	.037"-.042" [0.94 - 1.07]	2990003-01	2940231-01	2905014-01	MN370053.PDF
SS-37000-009	CAT5E	No	Not included - See boot PN: 450-034	.235" [5.97] Max	.042"-.048" [1.07 - 1.22]	2990003-01	2940231-01	2905014-01	MN370053.PDF
SS-37200-028	CAT5E	Yes	Not included - See boot PN: 450-011	.235" [5.97] Max	.037"-.042" [0.94 - 1.07]	2990003-01	2940231-01	2905014-01	MN370058.PDF
940-SP-3088R-A133	Cat5 / T1	No	Not included - See boot PN: 450-011	.235" [5.97] Max	.035"-.040" [0.89 - 1.02]	2990003-01	2940231-01	2905005-01	MN300015.PDF

Click for web page

Click for PDF



Termination Instructions available at stewartconnector.com

* Tool kits including Hand Tool and Die Set

Stewart has the widest selection of high performance modular plugs available on the market today, visit stewartconnector.com for our full product line offering.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Bel:

[2980078-01](#) [2905029-01](#) [2905014-01](#) [2980075-01](#) [2980070-01](#) [2940231-01](#)