

PLATING OPTIONS	PLATING DESCRIPTION
A	3.00 μm MIN TIN OVER 1.27MIN NICKEL OVERALL
E	0.38 μm MIN GOLD IN SELECTED AREA (2 SIDES) AND 3.00 μm MIN TIN IN SELECTED AREA AND 1.30 μm MIN NICKEL OVERALL
F	0.76 μm MIN GOLD IN SELECTED AREA (2 SIDES) AND 3.00 μm MIN TIN IN SELECTED AREA AND 1.30 μm MIN NICKEL OVERALL
G	0.05-0.10 μm GOLD FLASH IN SELECTED AREA (2 SIDES AND 3.00 μm MIN TIN IN SELECTED AREA AND 1.30 μm MIN NICKEL OVERALL