



- NOTES:
- PRODUCT SPEC. 108-5302
 - APPLICABLE CONTACT P/N
TAB CONTACT: 175150-[K*20-*16AWG]
175149-[K*25-*22AWG]
 - MATING CONN. P/N
PLUG HSG: 175278-[]
REC CONTACT: 175152-[K*20-*16AWG]
175151-[K*26-*22AWG]
 - INSTRUCTION SHEET, IS-503J
 - APPLICABLE PANEL THICKNESS, 0.8-2.0 (SEE FIG 1)
 - INSERT CONN. FROM PRESS DIRECTION SIDE FOR METAL PANEL.
 - EDGE OF THICKNESS WAY MUST NOT ROUND FOR MOLDED PANEL.

- 備考:
- 適用製品規格: 108-5302
 - 適用コンタクト型番
タブ・コンタクト: 175150-[K*20-*16AWG]
175149-[K*25-*22AWG]
 - 適合プラグ型番
プラグ・ハウジング: 175278-[]
リセ・コンタクト: 175152-[K*20-*16AWG]
175151-[K*26-*22AWG]
 - 取扱説明書: IS-503J
 - 適用パネル厚: 0.8-2.0 (FIG 1参照)
 - 金属パネルの場合、コネクタ取付方向をパンチ加工方向にしてください。
 - プラスチック、パネルの場合、穴縁部にRなき状態にしてください。

黒 (BLACK)	12	176299-9
青 (BLUE)	↑	↑ -6
黄 (YELLOW)	↓	↓ -4
赤 (RED)	↓	↓ -2
自然色 (NATURAL)	12	176299-1
ハウジング色調 (HOUSING COLOR)	極数 (Pos.)	型番 (P/N)

Copyright ©19 年		Copyright ©19 年 AMP (Japan), LTD. ALL RIGHTS RESERVED.		AMP 日本エレクトロニクス株式会社 Tokyo, Japan	
名称 (NAME) AMPユニバーサルパワーコネクタ 12極		3.96mmピッチ キャップ・ハウジング (パネル取付タイプ)		AMP UNIVERSAL POWER CONN. 3.96mm PITCH CAP HOUSING 12 Pos (PANEL MOUNT)	
材料 (MATERIAL) S/S タイロン (ULS4V-00) / S/S NYLON (ULS4V-00)		仕上げ (FINISH) 二色		一般公差	
A 改 訂 (1978) Y.N.M.S. 1/10/80		DR. Y. NARISAWA 1/25/80 DE. M. Shiki 1/25/80		SIZE LOC 番号 (No.)	
O 作 成 (1978) Y.N.M.S. 1/10/80		CHK. Y. Fujita 1/10/80 APP. J. O'Connell 1/10/80		A3 J C-176299	
LTR 変更 (REVISION RECORD)		DR CHK DATE		尺度 (SCALE) REV. SHEET	
				A A 1 OF 1	