




3879 - COMPACT MALE STUD ELBOW, BSP PARALLEL



maximum working pressure	20 bar 2 MPa 290 psi
working temperature	-25 to 150 °C -13 to 302 °F 248 to 423 °K
vacuum capability	755 mm Hg
body	STAINLESS STEEL 316L
sub-base	STAINLESS STEEL 316L
'O'-rings	FKM
collar	STAINLESS STEEL 316L
sealing washer	STAINLESS STEEL 316L

Part Nb	ØD (MM)	C (MM)	F (mm)	ØG (mm)	H (mm)	L (mm)	(kg)
	<input type="button" value="All"/>	<input type="button" value="All"/>	<input type="button" value="All"/>	<input type="button" value="All"/>	<input type="button" value="All"/>	<input type="button" value="All"/>	<input type="button" value="All"/>
3879 04 10	4	G1/8	13	11	22	19	.022
3879 04 13	4	G1/4	17	11	20	19	.027
3879 06 10	6	G1/8	13	12	24	24	.029
3879 06 13	6	G1/4	17	12	22	24	.034
3879 08 10	8	G1/8	13	15	25	25	.035
3879 08 13	8	G1/4	17	15	25	25	.039
3879 08 17	8	G3/8	21	15	23	25	.047
3879 10 13	10	G1/4	18	17	28.5	31	.057
3879 10 17	10	G3/8	21	17	28.5	31	.065
3879 12 13	12	G1/4	17	20	33	33	.077
3879 12 17	12	G3/8	21	20	33	33	.084
3879 12 21	12	G1/2	24	20	30	33	.096