

MS8239T	Range	Accuracy
Resistance	400Ω	±(1.2%+2)
	4KΩ, 40KΩ, 400KΩ, 4MΩ	±(1.0%+2)
	40MΩ	±(1.2%+8)
DCV	40mV	±(0.5%+5)
	400mV	±(0.5%+3)
	4V, 40V, 400V	±(0.8%+3)
	600V	±(1.0%+5)
ACV	40mV	±(1.0%+20)
	400mV	±(1.0%+10)
	4V, 40V, 400V	±(0.8%+3)
	600V	±(1.2%+5)
DCA	400uA, 4000uA, 40mA	±(1.0%+5)
	400mA	±(2.0%+5)
	4A, 10A	±(2.5%+5)
ACA	400uA	±(1.8%+3)
	4000uA, 40mA	±(1.5%+5)
	400mA	±(2.5%+5)
	4A, 10A	±(3.0%+10)

Frequency	10MHz	$\pm(0.1\%+2)$
°C	-20 °C ~ 750 °C	$\pm(2.0\%+3)$
°F	-4 °F ~ 1832 °F	$\pm(3.0\%+3)$
Capacitance	40.00nF	$\pm(4.0\%+25)$
	400.0nF ~ 400.0uF	$\pm(4.0\%+15)$
	4.000mF ~ 40.00mF	$\pm(5.0\%+25)$
Frequency	4.000Hz ~ 10MHz	$\pm(0.1\%+2)$