

Technical parameter	
Product model	NF-518
Product function	Wall detection function
Product appearance	Two-color mold, tough
screen type	2.4-inch high-definition color screen, Resolution 240*320
Charging method	support Type-C charging
Battery type	Polymer lithium battery (390mAh)
Voice broadcast	Live voice broadcast
Product size	63*25*139 (mm)
Product weight	200 ( g )
Wall detection function	
Depth measurement	Magnetic metal: 12cm
	Non-magnetic metal: 10cm
	Live (AC) wire: 5cm
	Wood: 3.8cm
Metal detection	Depth value is based on the $\phi$ 20mm standard steel pipe. Only for reference (Note: The error of the depth indication is forreference only)
Non-metal detection	√
AC detection	√
Automatic shutdown	5 minutes
Operating temperature	0°C~50°C
Storage temperature	-10°C~60°C