

**EURONORD AB 153410**



Sample photo

**Order symbol:** AB 153410  
**Product nbr:** 7083700  
**Description:** Enclosure, ABS  
**Remarks:** Grey cover

**EAN:** 6418074058867  
**EI. number:**  
 Finland: 3435484  
 Electric No. 8212003606  
 Denmark:  
 Electric No. Sweden: 7083700

Including: Base with screws for mounting plate/DIN-rail, cover with PUR gasket and stainless steel cover screws.

Dimensions:				Rating:
	Length	Width	Height	
mm:	340	150	101	Ingress Protection (EN 60529): IP66/IP67
inch:	13.4	5.9	4.0	Impact Resistance (EN 62262): IK07
Materials:				Electrical insulation: Totally insulated
<b>Material:</b>	ABS			Halogen free (DIN/VDE 0472, Part 815): 1
<b>Base colour:</b>	RAL 7035 -light grey			Flammability Rating: UL 94 HB
<b>Cover screws material:</b>	Stainless steel			Glow Wire Test (IEC 695-2-1) °C: 650
<b>Cover colour:</b>	RAL 7035 -light grey			NEMA Class: NEMA 1, 4, 4X, 12, 13
<b>Gasket material:</b>	Polyurethane			Certificates:
				SGS Fimko
Temperatures:				
<b>Temperature °C (short term):</b>	-40 ... 80 °C			
<b>Temperature °C (continuous):</b>	-40 ... 60 °C			
<b>Temperature °F (short term):</b>	-40 ... 175 °F			
<b>Temperature °F (continuous):</b>	-40 ... 140 °F			

EURONORD PC/ABS 340x150x101-121

