

Product finder

Search help

Search Pulse products by Keyword or Part number

Search

product groups connectors optical networking product sfpp-3130-l

[Back to results page](#)

SFPP-3130-L

Part number: SFPP-3130-L |  Active product [What is this?](#)



Application - LAN	
Connector Type	SFP CAGE & CONNECTOR
Speed	10GBASE-T
Number of Ports	2x2
Package	PRESS FIT

[Detailed info](#)

Documents

Data Sheets [Datasheet SFPP-3130-L.PDF](#)

Attributes

Connector Type	SFP CAGE & CONNECTOR
Contact Mating Area Plating	GOLD 30 u"
FRE Logo	NO
Housing Material	NYL ON +33% GF
Keyed	NO
LED Option	LIGHT PIPES
Latch	NOT APPLICABLE
Number of Contacts	20
Number of Ports	2x2
Number of Positions	20
PCB	NO PCB
PCB Mount Angle	SIDE ENTRY
Package	PRESS FIT
Package Height (mm)	25.3
Package Length (mm)	63.25
Package Width (mm)	29.06
Panel Stop	NO
Pin Shape	STAMPED/SQUARE
RoHS Compliant	YES - RoHS-6
Search	YES

Product Finder or Keyword

StockCheck Distributor Inventory

Find what you need

[Search Center](#)
[User Center](#)

[Application Support](#)
[Competitor XRef Search](#)
[IC XRef Search](#)
[Product Finder](#)
[Data Sheets](#)
[Contact Us](#)
[Distributors](#)
[Representatives](#)
[Offices](#)
[Quote/ Sample](#)
[Product Catalog](#)
[Literature Request](#)