

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0348033211](#)
Status: **Active**
Overview: [Stac64 Single, Multi-Pocket and Hybrid Header System](#)
Description: [CTX64 Female Terminal, Tin, S-Grip, D-Wind, Left Payoff, SAE 22](#)

Documents:

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)
[Brochure \(PDF\)](#)

General

| | |
|-------------------------|--|
| Product Family | Crimp Terminals |
| Series | 34803 |
| Application | Signal, Wire-to-Board |
| Crimp Quality Equipment | Yes |
| Overview | Stac64 Single, Multi-Pocket and Hybrid Header System |
| Product Name | CTX64 |
| UPC | 887191519272 |

Physical

| | |
|--------------------------------|----------------------|
| Gender | Female |
| Grip Code | S |
| Material - Metal | Copper Alloy |
| Material - Plating Mating | Tin |
| Material - Plating Termination | Tin |
| Net Weight | 0.114/g |
| Packaging Type | Reel |
| Termination Interface: Style | Crimp or Compression |
| Wire Insulation Diameter | 1.10 to 1.65mm |
| Wire Size AWG | 22 |
| Wire Size mm ² | 0.22-0.35 |

Electrical

| | |
|-------------------------------|------------------------------|
| Current - Maximum per Contact | See Receptacle Product Spec. |
| Voltage - Maximum | 14V DC |

Material Info



Series image - Reference only

EU ELV

Compliant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
D(2020)4578-DC (25
June 2020)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Compliant

Not Contained

Search Parts in this Series

[34803 Series](#)

Use With

[34729](#) 2.54mm Pitch Stac64 Right Angle Receptacle

Application Tooling | FAQ

Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global

| Description | Product # |
|-------------|-----------|
|-------------|-----------|

| | |
|---------------------|---------------------------|
| Hand Crimp Tool for | 638193700 |
|---------------------|---------------------------|

| | |
|---|--|
| CTX64 Receptacle Terminal, 0.22, 0.30, 0.35mm ² and 22 AWG | |
|---|--|

| | |
|-----------------------|---------------------------|
| FineAdjust Applicator | 639032600 |
|-----------------------|---------------------------|

| | |
|--|--|
| for CTX64 Mat Seal Receptacle Terminals, for Wire Process Use Only | |
|--|--|

This document was generated on 10/30/2020

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION