



JKL LAMP PART NO.	COLOR WHITE	STARTING CIRCUIT VOLTAGE VS (Vrms)	OPERATING LAMP VOLTAGE VL (Vrms)	OPERATING LAMP CURRENT IL (mA rms)	BRIGHTNESS (CANDELA/m <sup>2</sup> )	*RATED LIFE (HRS) MINIMUM
BF20170-38B	x = 0.356±0.02 y = 0.326±0.02	1000 @ 0°C	400	5	35,000 TYP.	20,000

\* RATED LIFE IS DEFINED AS THE POINT AT WHICH THE INTENSITY BECOMES 50% OF THE INITIAL RATING.

NOTE 1: MERCURY (Hg) CONTENT: 2.4mg/LAMP MAX.

		DIMENSIONS ARE IN MILLIMETERS TOLERANCE UNLESS OTHERWISE SPECIFIED 1 PL +/- 0.2 2 PL +/- 0 ANGLE +/- 0		<b>JKL COMPONENTS CORPORATION</b>			
		THIRD ANGLE PROJECTION		TITLE <b>MINIATURE COLD CATHODE FLUORESCENT LAMP</b>			
DRAWN BY L. WENGSTROM		APP'VD BY DATE L.R. 7/30/09		SIZE <b>A</b>	FSCM NO. <b>55335</b>	DRAWING NO. <b>BF20170-38B</b>	
- CAD DRAWING - MANUAL REVISIONS NOT PERMITTED		SCALE NONE		RELEASED DATE 12/15/04	REVISION DATE 7/30/09	REV. NO. <b>A</b>	SHEET 1 OF 1
REV. NO.	DESCRIPTION/ECO NUMBER	APP'VD DATE					
<b>A</b>	RATED LIFE HRS MINIMUM RELEASE & CANCEL P-0410-02	7/30/09 12/15/04					

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[JKL Components:](#)

[BF20170-38B](#)