



JKL PART NO.: CF20305-24B

JKL LAMP PART NO.	COLOR WHITE	STARTING CIRCUIT VOLTAGE VS (Vrms)	OPERATING LAMP VOLTAGE VL (Vrms)	OPERATING LAMP CURRENT IL (mA rms)	BRIGHTNESS (CANDELA/m <sup>2</sup> )	*RATED LIFE (HRS) (AVG.)
CF20305-24B	x = $0.278 \pm 0.01$ y = $0.264 \pm 0.01$	1750 @ 0°C	780	5	42,000 TYP.	40,000

\* RATED LIFE IS DEFINED AS THE POINT AT WHICH THE INTENSITY BECOMES 50% OF THE INITIAL RATING.

<p>METRIC THIRD ANGLE PROJECTION</p>			<p>DIMENSIONS ARE IN MILLIMETERS</p> <p>TOLERANCE UNLESS OTHERWISE SPECIFIED</p> <p>1 PL +/- 0.2 2 PL +/- 0 ANGLE +/- 0</p>		<p><b>JKL COMPONENTS CORPORATION</b></p>			
<p>TITLE</p> <p>MINIATURE COLD CATHODE FLUORESCENT LAMP</p>			SIZE	FSCM NO.	DRAWING NO.			
<p>DRAWN BY</p> <p>L. WENGSTROM</p>			<p>APPVD BY DATE</p> <p>L.R. 8/28/07</p>		A	55335	CF20305-24B	
<p>START VOLTS TO 2600 &amp; OPER. VOLT TO 1400</p> <p>8/23/07</p>			<p>RELEASED</p> <p>11/10/05</p>		<p>SCALE</p> <p>NONE</p>			
REV. NO.	DESCRIPTION/ECO NUMBER	APPVD DATE	<p>- CAD DRAWING -</p> <p>MANUAL REVISIONS NOT PERMITTED</p>		RELEASED DATE	REVISION DATE	REV. NO.	SHEET
					11/10/05	8/28/07	A	1 OF 1

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[JKL Components:](#)

[CF20305-24B](#)