



## **DEWALT DCS312N-XJ –**

### **12v XR Brushless Compact Reciprocating Saw – Bare Unit**



- Twist action keyless blade clamp for quick and easy blade change
- Ergonomic and rubber grip design for added comfort Improved, easy-to-read state of charge indicator
- Compact design allows better access to difficult-to-reach cuts
- Centrally positioned motor provides better balance, control, and ease of use
- LED for improved visibility of cut-line
- Intelligent variable speed trigger and lock off switch
- Brushless motor reduces tool size whilst maximising power delivery and providing extended runtime

#### **Description:**

The DEWALT DCS312D2-GB – 12v XR brushless compact reciprocating saw is compact and performance-packed. At only 1.38 kg (bare tool) and 308 mm in length and featuring an efficient brushless motor, it delivers up to 2800 SPM. This is combined with a 16 mm stroke length that offers fast and efficient cutting. The saw is equipped with an LED for visibility, a variable-speed trigger for added control, and a tool-free blade release for quick and easy blade changes.

#### **Supplied with:**

DEWALT DCS312D2-GB – 12v XR brushless compact reciprocating saw

<b>Specifications</b>	
No Load Stroke Rate	0 - 2800 spm
Max. Cutting Capacity (Wood)	90.0 mm
Max. Cutting Capacity (Steel Section & Pipes)	40.0 mm
Max. Cutting Capacity [PVC]	90.0 mm
Weight	1.38 kg
Battery Capacity	2.0 Ah
Battery Voltage	12 V
Sound Pressure	84.0 dB(A)
Sound Pressure Uncertainty	3.0 dB(A)
Sound Power	95.0 dB(A)
Sound Power Uncertainty	3.0 dB(A)
Hand/Arm Vibration - Cutting boards	5.7 m/s <sup>2</sup>
Uncertainty K 2 (Vibration)	1.6 m/s <sup>2</sup>