



# BZX84C2V4 SERIES

## SURFACE MOUNT SILICON ZENER DIODES

**VOLTAGE** 2.4 to 75 Volt **POWER** 410 mWatt

**SOT-23**


Unit : inch(mm)

### FEATURES

- Planar Die construction
- 410mW Power Dissipation
- Zener Voltages from 2.4~75V
- Ideally Suited for Automated Assembly Processes
- Lead free in compliance with EU RoHS 2.0
- Green molding compound as per IEC 61249 standard

### MECHANICAL DATA

- Case: SOT-23, Molded Plastic
- Terminals: Solderable per MIL-STD-750, Method 2026
- Approx. Weight: 0.0003 ounces, 0.0084 grams



## MAXIMUM RATINGS AND ELECTRICAL CHARACTERISTICS(T<sub>A</sub>=25°C unless otherwise noted)

| Parameter   | Symbol           | Value       | Units |
|---|------------------|-------------|-------|
| Maximum Power Dissipation (Notes 1) at 25°C               | P <sub>D</sub>   | 410         | mW    |
| Typical Thermal Resistance ,Junction to Ambient (Notes 2) | R <sub>θJA</sub> | 500         | °C/W  |
| Operating Junction and StorageTemperature Range           | T <sub>J</sub>   | -55 to +150 | °C    |

### NOTES:

1. Mounted on 50mmX16mm FR-4 board.
2. Mounted on minimum pad layout (1cmX1cm FR-4 board).





## BZX84C2V4 SERIES

| Part Number | Nominal Zener Voltage            |        |        | Max. Zener Impedance              |     |                                   |      | Max Reverse Leakage Current     |      | Marking Code |
|-------------|----------------------------------|--------|--------|-----------------------------------|-----|-----------------------------------|------|---------------------------------|------|--------------|
|             | V <sub>Z</sub> @ I <sub>ZT</sub> |        |        | Z <sub>ZT</sub> @ I <sub>ZT</sub> |     | Z <sub>ZK</sub> @ I <sub>ZK</sub> |      | I <sub>R</sub> @ V <sub>R</sub> |      |              |
|             | Nom. V                           | Min. V | Max. V | Ω                                 | mA  | Ω                                 | mA   | μA                              | V    |              |
| BZX84C2V4   | 2.4                              | 2.28   | 2.52   | 100                               | 5.0 | 600                               | 1.00 | 50                              | 1.0  | W1           |
| BZX84C2V7   | 2.7                              | 2.57   | 2.84   | 100                               | 5.0 | 600                               | 1.00 | 20                              | 1.0  | W2           |
| BZX84C3     | 3                                | 2.85   | 3.15   | 95                                | 5.0 | 600                               | 1.00 | 10                              | 1.0  | W3           |
| BZX84C3V3   | 3.3                              | 3.14   | 3.47   | 95                                | 5.0 | 600                               | 1.00 | 5.0                             | 1.0  | W4           |
| BZX84C3V6   | 3.6                              | 3.42   | 3.78   | 90                                | 5.0 | 600                               | 1.00 | 5.0                             | 1.0  | W5           |
| BZX84C3V9   | 3.9                              | 3.71   | 4.10   | 90                                | 5.0 | 600                               | 1.00 | 3.0                             | 1.0  | W6           |
| BZX84C4V3   | 4.3                              | 4.09   | 4.52   | 90                                | 5.0 | 600                               | 1.00 | 3.0                             | 1.0  | W7           |
| BZX84C4V7   | 4.7                              | 4.47   | 4.94   | 80                                | 5.0 | 500                               | 1.00 | 3.0                             | 2.0  | W8           |
| BZX84C5V1   | 5.1                              | 4.85   | 5.36   | 60                                | 5.0 | 480                               | 1.00 | 2.0                             | 2.0  | W9           |
| BZX84C5V6   | 5.6                              | 5.32   | 5.88   | 40                                | 5.0 | 400                               | 1.00 | 1.0                             | 2.0  | WA           |
| BZX84C6V2   | 6.2                              | 5.89   | 6.51   | 10                                | 5.0 | 150                               | 1.00 | 3.0                             | 4.0  | WB           |
| BZX84C6V8   | 6.8                              | 6.46   | 7.14   | 15                                | 5.0 | 80                                | 1.00 | 2.0                             | 4.0  | WC           |
| BZX84C7V5   | 7.5                              | 7.13   | 7.88   | 15                                | 5.0 | 80                                | 1.00 | 1.0                             | 5.0  | WD           |
| BZX84C8V2   | 8.2                              | 7.79   | 8.61   | 15                                | 5.0 | 80                                | 1.00 | 0.7                             | 5.0  | WE           |
| BZX84C8V7   | 8.7                              | 8.27   | 9.14   | 15                                | 5.0 | 100                               | 1.00 | 0.7                             | 5.0  | 87C          |
| BZX84C9V1   | 9.1                              | 8.65   | 9.56   | 15                                | 5.0 | 100                               | 1.00 | 0.5                             | 6.0  | WF           |
| BZX84C10    | 10                               | 9.50   | 10.50  | 20                                | 5.0 | 150                               | 1.00 | 0.2                             | 7.0  | WG           |
| BZX84C11    | 11                               | 10.45  | 11.55  | 20                                | 5.0 | 150                               | 1.00 | 0.1                             | 8.0  | WH           |
| BZX84C12    | 12                               | 11.40  | 12.60  | 25                                | 5.0 | 150                               | 1.00 | 0.1                             | 8.0  | WI           |
| BZX84C13    | 13                               | 12.35  | 13.65  | 30                                | 5.0 | 170                               | 1.00 | 0.1                             | 8.0  | WK           |
| BZX84C14    | 14                               | 13.30  | 14.70  | 30                                | 5.0 | 170                               | 1.00 | 0.1                             | 10.0 | WJ           |
| BZX84C15    | 15                               | 14.25  | 15.75  | 30                                | 5.0 | 200                               | 1.00 | 0.1                             | 10.5 | WL           |
| BZX84C16    | 16                               | 15.20  | 16.80  | 40                                | 5.0 | 200                               | 1.00 | 0.1                             | 11.2 | WM           |
| BZX84C17    | 17                               | 16.15  | 17.85  | 40                                | 5.0 | 200                               | 1.00 | 0.1                             | 12.2 | 17C          |
| BZX84C18    | 18                               | 17.10  | 18.90  | 45                                | 5.0 | 225                               | 1.00 | 0.1                             | 12.6 | WN           |
| BZX84C20    | 20                               | 19.00  | 21.00  | 55                                | 5.0 | 225                               | 1.00 | 0.1                             | 14.0 | WO           |
| BZX84C22    | 22                               | 20.90  | 23.10  | 55                                | 5.0 | 250                               | 1.00 | 0.1                             | 15.4 | WP           |
| BZX84C24    | 24                               | 22.80  | 25.20  | 70                                | 5.0 | 250                               | 1.00 | 0.1                             | 16.8 | WR           |
| BZX84C27    | 27                               | 25.65  | 28.35  | 80                                | 5.0 | 300                               | 1.00 | 0.1                             | 18.9 | WS           |
| BZX84C28    | 28                               | 26.60  | 29.40  | 80                                | 5.0 | 300                               | 1.00 | 0.1                             | 20.5 | 28C          |
| BZX84C30    | 30                               | 28.50  | 31.50  | 80                                | 5.0 | 300                               | 1.00 | 0.1                             | 21.0 | WT           |
| BZX84C33    | 33                               | 31.35  | 34.65  | 80                                | 5.0 | 325                               | 1.00 | 0.1                             | 23.1 | WU           |
| BZX84C36    | 36                               | 34.20  | 37.80  | 90                                | 5.0 | 350                               | 1.00 | 0.1                             | 25.2 | WW           |
| BZX84C39    | 39                               | 37.05  | 40.95  | 130                               | 5.0 | 350                               | 1.00 | 0.1                             | 27.3 | WX           |
| BZX84C43    | 43                               | 40.85  | 45.15  | 150                               | 5.0 | 375                               | 1.00 | 0.1                             | 30.1 | WY           |
| BZX84C47    | 47                               | 44.65  | 49.35  | 170                               | 5.0 | 375                               | 1.00 | 0.1                             | 32.9 | WZ           |
| BZX84C51    | 51                               | 48.45  | 53.55  | 100                               | 5.0 | 400                               | 1.00 | 0.1                             | 38.0 | XA           |
| BZX84C56    | 56                               | 53.20  | 58.80  | 135                               | 2.5 | 1000                              | 1.00 | 0.1                             | 42.0 | X2           |
| BZX84C62    | 62                               | 58.90  | 65.10  | 150                               | 2.5 | 1000                              | 1.00 | 0.1                             | 46.0 | X3           |
| BZX84C68    | 68                               | 64.60  | 71.40  | 200                               | 2.5 | 1000                              | 1.00 | 0.1                             | 51.0 | X4           |
| BZX84C75    | 75                               | 71.25  | 78.75  | 250                               | 2.5 | 1000                              | 1.00 | 0.1                             | 56.0 | X5           |



# BZX84C2V4 SERIES



Fig.1 STEADY STATE POWER DERATING



Fig.2 TEMPERATURE COEFFICIENTS




Fig.3 TYPICAL LEAKAGE CURRENT




Fig.4 TYPICAL FORWARD VOLTAGE



# BZX84C2V4 SERIES

## MOUNTING PAD LAYOUT

**SOT-23**

Unit : inch(mm)



## ORDER INFORMATION

- Packing information
  - T/R - 12K per 13" plastic Reel
  - T/R - 3K per 7" plastic Reel



# BZX84C2V4 SERIES


## Part No\_packing code\_Version

BZX84C2V4\_R1\_00001

BZX84C2V4\_R2\_00001

For example :

**RB500V-40\_R2\_00001**



| Packing Code <b>XX</b>               |                      |                                  |                      | Version Code <b>XXXXX</b> |                      |                                       |
|--------------------------------------|----------------------|----------------------------------|----------------------|---------------------------|----------------------|---------------------------------------|
| Packing type                         | 1 <sup>st</sup> Code | Packing size code                | 2 <sup>nd</sup> Code | HF or RoHS                | 1 <sup>st</sup> Code | 2 <sup>nd</sup> -5 <sup>th</sup> Code |
| Tape and Ammunition Box (T/B)        | <b>A</b>             | N/A                              | <b>0</b>             | <b>HF</b>                 | <b>0</b>             | serial number                         |
| Tape and Reel (T/R)                  | <b>R</b>             | 7"                               | <b>1</b>             | <b>RoHS</b>               | <b>1</b>             | serial number                         |
| Bulk Packing (B/P)                   | <b>B</b>             | 13"                              | <b>2</b>             |                           |                      |                                       |
| Tube Packing (T/P)                   | <b>T</b>             | 26mm                             | <b>X</b>             |                           |                      |                                       |
| Tape and Reel (Right Oriented) (TRR) | <b>S</b>             | 52mm                             | <b>Y</b>             |                           |                      |                                       |
| Tape and Reel (Left Oriented) (TRL)  | <b>L</b>             | PANASERT T/B CATHODE UP (PBCU)   | <b>U</b>             |                           |                      |                                       |
| FORMING                              | <b>F</b>             | PANASERT T/B CATHODE DOWN (PBCD) | <b>D</b>             |                           |                      |                                       |



## **BZX84C2V4 SERIES**

---

### **Disclaimer**

- Reproducing and modifying information of the document is prohibited without permission from Panjit International Inc..
- Panjit International Inc. reserves the rights to make changes of the content herein the document anytime without notification. Please refer to our website for the latest document.
- Panjit International Inc. disclaims any and all liability arising out of the application or use of any product including damages incidentally and consequentially occurred.
- Panjit International Inc. does not assume any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.
- Applications shown on the herein document are examples of standard use and operation. Customers are responsible in comprehending the suitable use in particular applications. Panjit International Inc. makes no representation or warranty that such applications will be suitable for the specified use without further testing or modification.
- The products shown herein are not designed and authorized for equipments requiring high level of reliability or relating to human life and for any applications concerning life-saving or life-sustaining, such as medical instruments, transportation equipment, aerospace machinery et cetera. Customers using or selling these products for use in such applications do so at their own risk and agree to fully indemnify Panjit International Inc. for any damages resulting from such improper use or sale.
- Since Panjit uses lot number as the tracking base, please provide the lot number for tracking when complaining.

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Panjit:](#)

[BZX84C18\\_R1\\_00001](#) [BZX84C18\\_R1\\_10001](#) [BZX84C18\\_R2\\_00001](#) [BZX84C18\\_R2\\_10001](#)