


FNMK4

Cap
60° Cone

Mates with D9 style hose fitting



| TUBE FITTING PART # | END SIZE | C HEX (mm) | L (mm) | L1 (mm) | STANDARD Dynamic Pressure (x 1,000 PSI) |
|---------------------------|-----------|------------------|-----------|------------|--|
| | 1 BSPP | | | | S |
| 2FNMK4 | 1/8 | 14 | 16.0 | 11.9 | 5.1 |
| 4FNMK4 | 1/4 | 19 | 20.6 | 15.1 | 5.1 |
| 6FNMK4 | 3/8 | 22 | 22.3 | 15.8 | 5.1 |
| 8FNMK4 | 1/2 | 27 | 22.7 | 18.6 | 2.9 |
| 10FNMK4 | 5/8 | 30 | 26.6 | 17.1 | 2.9 |
| 12FNMK4 | 3/4 | 32 | 28.0 | 19.0 | 2.9 |
| 16FNMK4 | 1 | 41 | 31.6 | 20.5 | 1.7 |
| 20FNMK4 | 1 1/4 | 50 | 35.9 | 25.5 | 1.5 |
| 24FNMK4 | 1 1/2 | 60 | 37.9 | 24.6 | 1.5 |

Dimensions and pressures for reference only, subject to change.