


PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0430201001](#)
Status: **Active**
Overview: [Micro-Fit Connector System](#)
Description: Micro-Fit 3.0 Plug Housing, Dual Row, 10 Circuits, UL 94V-0, Low-Halogen, Black

Documents:

3D Model	Test Summary TS-43045-001-001 (PDF)
Drawing (PDF)	Test Summary TS-46235-001-001 (PDF)
Product Specification PS-43045 (PDF)	RoHS Certificate of Compliance (PDF)
Packaging Specification PK-43020-001-001 (PDF)	Product Literature (PDF)



Agency Certification

CSA	LR19980
UL	E29179

General

Product Family	Crimp Housings
Series	43020
3D Viewer	Yes
Application	Power, Wire-to-Wire
Overview	Micro-Fit Connector System
Product Literature Order No	987650-5984
Product Name	Micro-Fit 3.0
UPC	800754383509

Physical

Circuits (maximum)	10
Color - Resin	Black
Flammability	94V-0
Gender	Plug
Glow-Wire Capable	No
Keying to Mating Part	None
Lock to Mating Part	Yes
Material - Resin	Nylon
Net Weight	1.172/g
Number of Rows	2
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	3.00mm
Pitch - Termination Interface	3.00mm
Polarized to Mating Part	Yes
Stackable	No
Temperature Range - Operating	-40° to +105°C

Solder Process Data

Lead-freeProcess Capability	N/A
-----------------------------	-----

Material Info

Reference - Drawing Numbers

Packaging Specification	PK-43020-001-001
Product Specification	PS-43045
Sales Drawing	SDA-43020-XXXX
Test Summary	TS-43045-001-001, TS-46235-001-001

EU ELV

Compliant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
ED/71/2019 (16 July
2019)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Compliant

Not Contained

Search Parts in this Series

[43020 Series](#)

Mates With

Micro-Fit 3.0 Receptacle Housings [43025](#)

Micro-Fit 3.0 Cable Assembly [245132](#)

Use With

Micro-Fit 3.0 Male Crimp Terminals [43031](#)

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION