

CRIMPFOX CENTRUS 6S - Crimping pliers



1213144

<https://www.phoenixcontact.com/us/products/1213144>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Crimping pliers, for uninsulated and insulated ferrules, DIN 46228 Part 1 and 4, from 0.14 mm² ... 6 mm², also for TWIN ferrules up to 2 x 4 mm², automatic cross section adjustment, lateral insertion, equipped with fall protection

Your advantages

- Pressure lock ensures consistently high quality crimping results
- Ergonomic handle design ensures comfortable, fatigue-free handling
- With a particularly small handle width, the tool fits perfectly in your hand
- Up to 30 % lower actuation force, thanks to optimized leverage
- Sturdy plastic guard over the head of the pliers protects the tool against damage caused by dropping

Commercial data

| | |
|--------------------------------------|---------------------|
| Item number | 1213144 |
| Packing unit | 1 pc |
| Minimum order quantity | 1 pc |
| Sales key | BH31 |
| Product key | BH3131 |
| Catalog page | Page 420 (C-3-2019) |
| GTIN | 4055626212678 |
| Weight per piece (including packing) | 459.2 g |
| Weight per piece (excluding packing) | 379.2 g |
| Customs tariff number | 82032000 |
| Country of origin | SE |

CRIMPFOX CENTRUS 6S - Crimping pliers



1213144

<https://www.phoenixcontact.com/us/products/1213144>

Technical data

Notes

| | |
|----------------------------------|---|
| General | DIN 46228-1, DIN 46228-4 |
| Environmental Product Compliance | |
| California Proposition 65 | Further information on California's prop. 65 is available under "Downloads" in the manufacturer's declaration |

Product properties

| | |
|---------------------|---|
| Product type | Crimping tool |
| Compression | Square crimp |
| Area of application | TWIN ferrules up to 2 x 4 mm ² |

Crimping position 1

| | |
|--------------------|----------------------|
| Min. cross section | 0.14 mm ² |
| Max. cross section | 6 mm ² |
| AWG min | 26 |
| AWG max | 10 |

Electrical properties

| | |
|------|-----------------------------------|
| Fuse | DIN 46228-1, DIN 46228-4, UL 486F |
|------|-----------------------------------|

Connection data

Conductor connection

| | |
|-----------------------------|--|
| Cross section range, metric | 0.14 mm ² ... 6 mm ² |
| Cross section range AWG | 26 ... 10 |

Dimensions

| | |
|--------|--------|
| Width | 70 mm |
| Height | 21 mm |
| Length | 180 mm |

Material specifications

| | |
|-------|-------------|
| Color | black/green |
|-------|-------------|

CRIMPFOX CENTRUS 6S - Crimping pliers



1213144

<https://www.phoenixcontact.com/us/products/1213144>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1213144>



EAC

Approval ID: RU x-DE.xx08.B.02974

CRIMPFOX CENTRUS 6S - Crimping pliers



1213144

<https://www.phoenixcontact.com/us/products/1213144>

Classifications

ECLASS

| | |
|-------------|----------|
| ECLASS-11.0 | 21043811 |
| ECLASS-12.0 | 21043811 |
| ECLASS-13.0 | 21043811 |

ETIM

| | |
|----------|----------|
| ETIM 9.0 | EC000168 |
|----------|----------|

UNSPSC

| | |
|-------------|----------|
| UNSPSC 21.0 | 27111500 |
|-------------|----------|

CRIMPFOX CENTRUS 6S - Crimping pliers



1213144

<https://www.phoenixcontact.com/us/products/1213144>

Accessories

CRIMPFOX/ SPR-4 - Replacement spring

1200288

<https://www.phoenixcontact.com/us/products/1200288>

Spare recuperating spring



CRIMPFOX CENTRUS NC/U-HANDLE - Replacement handle

1202880

<https://www.phoenixcontact.com/us/products/1202880>

Replacement upper handle for CRIMPFOX CENTRUS series



Phoenix Contact 2024 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com