



## PROFIBUS Field Attachable Connectors


### 0976 PFC 101



#### M12 Female (Screw Terminals)

Field attachable connector, M12 female connector with threaded joint, shieldable, assembling with screw terminals 0976 PFC 101: 5 poles, B coding.

– especially suitable for Profibus signal cable 0975 254 000/... M –



\*a O-Ring


### 0976 PFC 102



#### M12 Female (Spring-Type Terminals)

Field attachable connector, M12 female connector with threaded joint, shieldable, assembling with spring-type terminals 0976 PFC 102: 4 poles, B coding.

– especially suitable for Profibus signal cable 0975 254 000/...M Profibus signals –



\*a O-Ring

### Pin Assignment

#### M12 - 4 Poles (B-Code)



#### M12 - 5 Poles (B-Code)





Be Certain with Belden

**PROFIBUS Field Attachable Connectors**

0976 PFC 101 | 0976 PFC 102

**Technical Data**

**Environmental**






Degree of protection IP 67 / NEMA 6P  
 Operating temperature range -25°C (-13°F) / +90°C (+194°F)

**Mechanical**

Housing / Molded body GD-ZnAl, pre-coppered and nickel-plated  
 Insert PBT  
 Contact 0976 PFC 101: CuZn, pre-coppered, CuSnZn  
 0976 PFC 102: Stainless steel, silver-plated, gold plated  
 Receptacle shell CuZn, nickel-plated  
 Shield sleeve CuBe, tin-plated  
 O-ring FKM  
 Mode of connection 0976 PFC 101: screw terminals  
 0976 PFC 102: spring-type terminals  
 Connectable conductor 0976 PFC 101: max. 0.75 mm<sup>2</sup>  
 0976 PFC 102: 0.14-0.50 mm<sup>2</sup>, 0.14 mm<sup>2</sup> with terminal pin sleeve

**Electrical**

Contact resistance ≤ 5 mΩ  
 Nominal current at 40°C 4 A  
 Nominal voltage 4 poles 120 V  
 5 poles 60 V  
 0976 PFC 102: 32 V  
 Rated voltage 4 poles 125 V  
 5 poles 63 V  
 Test voltage 4 poles 1.5 kV eff. / 60 s  
 5 poles 1.0 kV eff. / 60 s  
 0976 PFC 102: 0.65 kV eff. / 60 s  
 Insulation resistance > 10<sup>9</sup> Ω  
 Pollution degree 3

Part Number	Pins	Screw Joint for Cable			
0976 PFC 101	5B	Ø 4.0-9.0 mm			
0976 PFC 102	4B	Ø 4.0-9.0 mm			

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Lumberg Automation:](#)

[0976 PFC 102](#) [0976 PFC 101](#)