

NYS352

Heavy duty phono plug, cable clamp





Article Variations

| Article Name | Details | Packaging |
|--------------|--|-----------|
| NYS352 | Nickel plated shell and contacts | |
| NYS352AG | Gold plated shell and contacts | |
| NYS352B | Black plated shell, nickel plated contacts | |
| NYS352BG | Black plated shell, gold plated contacts | |
| NYS352G | Nickel plated shell, gold plated contacts | |

Technical Information

| Product | |
|------------------------|--------|
| Title | NYS352 |
| Connection Type | Plug |

| Electrical | |
|------------------------------|----------------------------|
| Contact resistance | $\leq 10\text{m}\Omega$ |
| Insulation resistance | $\geq 2,000\text{M}\Omega$ |
| Dielectric strength | 50Hz 0.5KVdc |

| Mechanical | |
|---------------------------------------|----------------------|
| Insertion and Withdrawal force | 5-20N |
| Lifetime | >5,000 mating cycles |

| Material | |
|--------------------|----------------|
| Pin | Brass |
| Housing | Brass |
| Housing | Zinc |
| Insulation | PP |
| Cable Clamp | Steel |
| Pin | Tin and Cer |
| Cable Clamp | Tin and Cer |
| Housing | Nickel Plating |
| Housing | Nickel Plating |