

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: **0430315003**
Status: **Active**
Overview: Micro-Fit Connector System
Description: Micro-Fit TPA Crimp Terminal, Male, with Tin (Sn) Pre-plated Phosphor Bronze Contact, 20-24 AWG, Reel

Documents:

Drawing (PDF)	Packaging Specification PK-43031-001-001 (PDF)
Product Specification 436500001-PS-JA-000 (PDF)	Test Summary 430450005-TS-000 (PDF)
Product Specification 436500001-PS-KO-000 (PDF)	Test Summary TS-43045-001-001 (PDF)
Product Specification 436500001-PS-SP-000 (PDF)	Datasheet (PDF)
Product Specification PS-43650-001 (PDF)	RoHS Certificate of Compliance (PDF)

General

Product Family	Crimp Terminals
Series	43031
Application	Power, Wire-to-Wire
Crimp Quality Equipment	Yes
Overview	<u>Micro-Fit Connector System</u>
Product Name	Micro-Fit TPA
Taxonomy	Crimp Terminals
UPC	889056917179

Physical

Durability (mating cycles max)	30
Gender	Male
Material - Metal	Phosphor Bronze
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Net Weight	0.061/g
Packaging Type	Reel
Plating min - Mating	1.000µm
Plating min - Termination	1.000µm
Termination Interface: Style	Crimp or Compression
Wire Insulation Diameter	1.85mm max.
Wire Size AWG	20, 22, 24
Wire Size mm ²	N/A

Electrical

Current - Maximum per Contact	8.5A
-------------------------------	------

Material Info

Reference - Drawing Numbers

Packaging Specification	PK-43031-001-001
Product Specification	436500001-PS-JA-000, 436500001-PS-KO-000, 436500001-PS-SP-000, PS-43650-001
Sales Drawing	430310000-SD-000
Test Summary	430450005-TS-000, TS-43045-001-001



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
D(2022)4187-DC (10
June 2022)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Not Relevant

Not Contained

Search Parts in this Series

43031 Series

Use With

Micro-Fit TPA Plug Housing [200875](#)

Application Tooling | FAQ

Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global

Description	Product #
Extraction Tool for Micro-Fit Terminals	11030043
Hand Crimp Tool for Micro-Fit Crimp Terminals, 20 AWG, UL1007 and UL1061 Wires	2133094500
Hand Crimp Tool for Micro-Fit Crimp Terminals, 22 AWG,	2133094600

UL1007 and UL1061
Wires
Hand Crimp Tool 2133094700
for Micro-Fit+ Crimp
Terminals, 24 AWG,
UL 1007 and UL
1061 Wires
Insertion Tool for 638120800
Micro-Fit 3.0 and
CRC Male and
Female Crimp
Terminals, 20-30
AWG
FineAdjust Applicator639004500
for Insulation OD
1.30-1.85mm, 20-24
AWG Wire
FineAdjust Applicator639018800
for Insulation OD
1.10-1.30mm - 20-24
AWG
FineAdjust Applicator639018900
for Micro-Fit 3.0
Terminals, for 20-24
AWG Wire with
Insulation Diameter
0.91-1.09mm
T2 Terminator 639104500
for Insulation OD
1.30-1.85mm, 20-24
AWG
T2 Terminator 639118800
for insulation OD
1.10-1.30mm - 20-24
AWG
T2 Terminator 639118900
for insulation OD
0.91-1.09mm - 20-24
AWG

This document was generated on 10/27/2022

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION