



### RE932

- Epoxy fibre-glass FR41.50 mm
- Double-sided 35 µm Cu
- Plated through holes (PTH)
- Surface chem. Ni/Au with solder stop mask
- Adaption circuit board for 10 different SO's
- Pitch: 1.27 mm
- Hole diameter 1.00 mm
- Prescratched rated break point for the separation of individual modules from the board
- Size 58.50 x 88.00 mm

Module-No.	Pitch	mil	Pin	Size (mm)
RE932-01	1.270 mm	0.50	8	3.90 (153 mil)
RE932-02	1.270 mm	0.50	8-w	7.50 (295 mil)
RE932-03	1.270 mm	0.50	14	3.90 (153 mil)
RE932-04	1.270 mm	0.50	16	3.90 (153 mil)
RE932-05	1.270 mm	0.50	16-w	7.50 (295 mil)
RE932-06	1.270 mm	0.50	20-w	7.50 (295 mil)
RE932-07	1.270 mm	0.50	24-w	7.50 (295 mil)
RE932-08	1.270 mm	0.50	28-w	7.50 (295 mil)
RE932-09	1.270 mm	0.50	32	7.50 (295 mil)
RE932-10	1.270 mm	0.50	40 (SOJ)	10.16 (400 mil)