



Model 4288
Adapter, SMA Male to BNC Male



Materials

Body: Beryllium Copper
 Contacts: Male – Brass
 Finish: SMA Body – Gold Plated per MIL-G-45204, Type II, Class 2
 BNC Body – Nickel Plated per QQ-N-290
 Contacts – Gold Plated per MIL-G-45204, Type II, Class 2
 Dielectric: PTFE per L-P-403



Specifications

Voltage: For *CE Compliance* and for personal safety, do not hold in hand when voltages exceed 33 Vrms/70 Vdc.
 Maximum voltage for *hands free use*: 335 Vrms Max.
 Operating Temperature: -65°C (-85°F) to +165°C (+329°F)
 Nominal Impedance: 50 Ohms
 Frequency Range: 0 – 12.4 GHz.

Ordering Information

Model: 4288

USA: Sales: 800-490-2361
 Technical Support: technicalsupport@pomonatest.com
 Fax: 425-446-5844
Europe: 31-(0) 40 2675 150 **International:** 425-446-5500
Where to Buy: www.pomonaelectronics.com

All dimensions are in inches. Tolerances (except noted): .xx = ±.02" (.51 mm),
 .xxx = ±.005" (.127 mm). All specifications are to the latest revisions.
 Specifications are subject to change without notice. Registered trademarks are
 the property of their respective companies.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Pomona:](#)

[4288](#)