


P	LTR	DESCRIPTION	DATE	DWN	APVD
A		RELEASE TO PRODUCTION	29NOV2019	AY	PS

NOTES:


- MATERIAL
HOUSING : HIGH TEMPERATURE THERMOPLASTIC, UL94-V0; COLOR- BLACK
CONTACT PIN : COPPER ALLOY
FINISH :
MATING SIDE : MIN. 0.1 μm GOLD OVER NICKEL UNDER PLATING.
SOLDER SIDE : MIN. 2.0 μm TIN OVER NICKEL UNDER PLATING.
 - PACKAGING: TUBE.
- △ TOLERANCE NOT CUMULATIVE.




2-2842248-0 AS SHOWN

CONTACT PIN	ITEM NO.
2	1
DESCRIPTION	ITEM NO.

DIM "G"	DIM "F"	DIM "E"	POS.	TE PN
44	50.85	52.65	50	5-2842248-0
38	44.85	46.65	44	4-2842248-4
34	40.85	42.65	40	4-2842248-0
28	34.85	36.65	34	3-2842248-4
24	30.85	32.65	30	3-2842248-0
20	26.85	28.65	26	2-2842248-6
18	24.85	26.65	24	2-2842248-4
14	20.85	22.65	20	2-2842248-0
10	16.85	18.65	16	1-2842248-6
8	14.85	16.65	14	1-2842248-4



RECOMMENDED PCB HOLE PATTERN FOR THROUGH HOLE WAVE



RECOMMENDED PCB HOLE PATTERN FOR THROUGH HOLE REFLOW/PIN-IN-PASTE

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN SUBHASREE S 16AUG2019
DIMENSIONS: mm		CHK KARTHIK JK 19AUG2019
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD PRASHANTH S 19AUG2019
0 PLC	±	PRODUCT SPEC 108-64040
1 PLC	±	APPLICATION SPEC 114-32259
2 PLC	±0.25	WEIGHT -
3 PLC	±	CUSTOMER DRAWING
4 PLC	±	SCALE 5:1
ANGLES	±2°	SHEET 1 OF 1
FINISH	SEE NOTES	REV A
MATERIAL	SEE NOTES	

TE TE Connectivity

NAME AMPMODU 2mm SHROUDED HEADER, DUAL ROW, RIGHT ANGLE, 0.1 Au, TUBE

SIZE A3 CAGE CODE 00779 DRAWING NO C-2842248 RESTRICTED TO -

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[1-2842248-4](#)