

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: **0501258000**
Status: **Active**
Overview: PicoBlade™ Connector System
Description: 1.25mm Pitch PicoBlade™ Crimp Terminal 50125, 26-28 AWG, Reel

Documents:

[3D Model](#) [Product Specification PS-51021-009-001 \(PDF\)](#)
[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

General

Product Family	Crimp Terminals
Series	50125
Application	Signal
Crimp Quality Equipment	Yes
Current Derating Order No	987651-3691
Overview	PicoBlade™ Connector System
Packaging Alternative	50125-8100 (Loose)
Product Name	PicoBlade™
UPC	800753630260

Physical

Gender	Male
Material - Metal	Phosphor Bronze
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Net Weight	17.100/mg
Packaging Type	Reel
Plating min - Mating	0.889µm
Plating min - Termination	0.914µm
Termination Interface: Style	Crimp or Compression
Wire Insulation Diameter	0.50-1.00mm
Wire Size AWG	26, 28
Wire Size mm²	N/A


Electrical

Current - Maximum per Contact	1.0A
Voltage - Maximum	125V

Material Info

Reference - Drawing Numbers

Crimp Specification	CS-50125_50133
Product Specification	PS-51021-009-001
Sales Drawing	SD-50125-8*00



EU ELV

Compliant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
ED/21/2016 (20 June
2016)

Halogen-Free

Status

Low-Halogen

Need more information on product environmental compliance?

Email productcompliance@molex.com
Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS	Green Image
ELV	Compliant
RoHS Phthalates	Not Contained

Search Parts in this Series

[50125 Series](#)

Mates With

[50058 Crimp Terminal](#), [50079 Crimp Terminal](#)

Use With

[51047 Crimp Housing](#)