

Item no.: 264-701
 Product description: 2-CONDUCTOR MINIATURE THROUGH TERMINAL BLOCK;
 CENTRE MARKING; for DIN 15 rail; FRONT-ENTRY; CAGE
 CLAMP®CONNECTION; HORIZONTAL TYPE



Packing unit 100 pieces

Product group	9 (Std Chassis Mt Blocks)
Cross section from [mm ²]	0,08 mm ²
Cross section to [mm ²]	2,5 mm ²
Cross section from [AWG]	28 AWG
Cross section to [AWG]	12 AWG
Connection method	CAGE CLAMP®CONNECTION
Measured voltage EN	800 V
Measured shock voltage	8 kV
Pollution degree	3
Current intensity EN	24 A
Weight	3,9 g
Color	grey
Wiring type	Front-entry
No. of connection Points	2
No. of potentials	1
Height	24,5 mm
Height	0,96 in
Width	6 mm
Width	0,236 in
Depth	32 mm
Depth	1,26 in
Strip length from	8 mm
Strip length to	9 mm
Strip length	0,33 in



Item number	Admission office	Approval no.	Voltage [V]	Current [A]	Cross section [mm ²]
264-701	ABS	04-HG476174-PDA	800	24	2,5
264-701	BV	07436/C0			0,08-2,5
264-701	CCA	NL5704	800		2,5
264-701	CSA	18677-23	600	20	26-12
264-701	DNV	E7569	800	24	2,5
264-701	GL	17295-00HH	800	24	4
264-701	KEMA	2079570.01	800		2,5
264-701	KR	HMB05880-EL002	800	24	
264-701	LR	92/20242(E5)	800	24	2,5
264-701	PRS	TE/1718/880590/08	800		2,5
264-701	RMR	11130002	800	24	2,5
264-701	UR	E45172	600	20	28-12

Sorting criteria: admission office - approval number

© WAGO Kontakttechnik GmbH & Co. KG

Specifications are subject to changes and errors may be expected