

Product data sheet

Specifications



Mureva BOX - junction box - knock-out 8xM12/16+4xM16/20+2xM20/25 - 150x105x80 mm

ENN05087

Main

Product range	Mureva BOX
Product type	Junction box
Colour	Grey (RAL 7035)
Quantity per package	1 piece

Complementary

Mounting	Surface
Cable entry	Knock-out
Fixing mode	Screw-fixed: cover
Inner dimensions	150 x 105 x 80 mm
Number of cable entries	4 x M16/20 8 x M12/16 2 x M20/25
Material	PP (polypropylene): body and cover
Electrical insulation class	Class II conforming to IEC 536
Height	120 mm
Width	85 mm
Depth	165 mm
Net weight	0.28 kg

Environment

Operating temperature	-25...40 °C
IP-Class	IP55 conforming to IEC 60529
IK-Class	IK07 conforming to EN 50102
Glow wire temperature	750 °C
Standards	EN 60670 CE

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1

Package 1 Height	8.5 cm
Package 1 Width	12 cm
Package 1 Length	16.5 cm
Package 1 Weight	280 g
Unit Type of Package 2	CAR
Number of Units in Package 2	40
Package 2 Height	40 cm
Package 2 Width	40 cm
Package 2 Length	60 cm
Package 2 Weight	12.16 kg
Unit Type of Package 3	PAM
Number of Units in Package 3	1000
Package 3 Height	215 cm
Package 3 Width	100 cm
Package 3 Length	120 cm
Package 3 Weight	303.5 kg

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile

Contractual warranty

Warranty	18 months
----------	-----------

Recommended replacement(s)