



SPECIFICATION

- 1. Rated Voltage 1.5 V
- 2. Operating Voltage 1~2 V
- 3. Max. Rated Current 10mA
- 4. Coil Resistance 50±7.5Ω
- 5. Coil Impedance 140 Ω
- 6. Min. Sound Pressure Level 80dB/10cm
- 7. Resonant Frequency 2048Hz
- 8. Case Material NORYL
- 9. Operating Temperature -20~+70°C
- 10. Store Temperature -30~+80°C
- 11. Weight 2g

KEPO NINGBO KEPO ELECTRONIC CO.,LTD http://www.chinaacoustic.com									
Magnetic Buzzer KP12-185CL									
No.	DESCRIPTION	APPROVED	DATE	DRAWN	CHECKED	APPROVED	DATE	UNIT	DRAWING
	FORMER DRAWING							mm	KP3,8,40,663,01
	FORMER DRAWING							SCALE	SHEET
	FORMER DRAWING						05.08.01	NOT TO SCALE	VER 1.0